

TECHSPEC[®] 350nm 50mm Dia., High Performance Longpass Filter



High Performance OD 4.0 Longpass Filters

Stock **#34-300** 3-4 DAYS

-

1

+

€551⁰⁰

ADD TO CART

Qty 1-5
€551,00
Qty 6+
€472,00
Volume Pricing
Request Quote
ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Longpass Filter


Type:

Physical & Mechanical Properties	
50.00 +0/-0.2	Diameter (mm):
1.50	Thickness (mm):
±0.1	Thickness Tolerance (mm):
>80	Clear Aperture (%):
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2	
Optical Properties	
0	Angle of Incidence (°):
≥4.0	Optical Density OD (Average):
350.00	Cut-On Wavelength (nm):
Fused Silica (Corning 7980)	Substrate:
Hard Coated	Coating:
200 - 340	Rejection Wavelength (nm):
60-40	Surface Quality:
>91	Transmission (%):
358 - 1600	Transmission Wavelength (nm):
≤λ/4 @ 633nm (prior to coating)	Transmitted Wavefront, RMS:
±1	Cut-On Tolerance (%):
1.00	Slope Factor (%):
Surface 1: Hard Dielectric Sputtered Surface 2: AR Coated	Coating Specification:
200 - 1600	Wavelength Range (nm):
Environmental & Durability Factors	
Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7	Environmental Durability:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

PRODUCT DETAILS

- Cut-On Slope <1%
 - Rejection OD ≥ 4.0
 - ≥91% Transmission in Pass Band
 - Variety of [OD 4.0 Longpass Filter Kits](#) Available
- TECHSPEC® High Performance OD 4.0 Longpass Filters feature high transmission in the pass band combined with superior blocking in the rejection band. Due to a rejection band optical density of 4.0 combined with >91% in the pass band, these filters are ideal for a wide variety of applications. TECHSPEC® High Performance OD 4.0 Longpass Filters are hard coated, with a hard dielectric sputtered as the first surface and AR coating as the second. Eliminate straylight by creating custom bandpass filters when combined with [TECHSPEC® High Performance Shortpass Filters](#).
- Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.
- [TECHSPEC® Rotating Filter Wheel](#) can be used for applications requiring a variety of filters.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS