

TECHSPEC® 355nm, 12.5mm Diameter, Raman Edge Filter



Stock **#86-218** [CONTACT US](#)

⊖ 1 ⊕ **€505,00**

ADD TO CART

Qty 1-9
€505,00
Qty 10+
€420,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm): 358.60
Design Wavelength DWL (nm): 355
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >90
Type: Longpass Filter
Transition Width (nm): <3.6
Clear Aperture (%): >80
Durability: Environmental: MIL-STD-810F Physical: MIL-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >400
Coating Specification: T _{abs} ≥93% @ 364 - 400nm T _{avg} ≥90% @ 364 - 800nm
Wavelength Range (nm): 355 - 800
Laser Blocking Wavelength (nm): 355.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View