


[See all 10 Products in Family](#)

## 38.1mm Dia., Aluminum Coated, Aluminum Substrate Mirror



Metal Substrate Mirrors

Stock #47-115 **20+ In Stock**

⊖ 1 ⊕ €238.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	€238,00 each
Qty 6-25	€215,00 each
Qty 26-49	€203,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Flat Mirror **Type:**

### Physical & Mechanical Properties

38.10 +0.00/-0.38 **Diameter (mm):**

**Thickness (mm):**

9.50

Clear Aperture (%):

90

Surface Roughness (Å):

<175

### Optical Properties

Wavelength Range (µm):

0.4 - 12

Coating Type:

Metal

Coating:

Protected Aluminum (400-12000nm)

Wavelength Range (nm):

400 - 12000

Substrate: □

Aluminum 6061-T6

Coating Specification:

R<sub>avg</sub> >85% @ 400 - 700nm  
R<sub>avg</sub> >70% @ 700 - 2000nm  
R<sub>avg</sub> >97% @ 2 - 12µm

Surface Quality:

80-50

Surface Flatness (RMS):

λ/4

### Threading & Mounting

Mounting Threads:

6-32 TPI Tapped Holes

### Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant


## Product Details

- Aluminum Substrate Mirrors
- Ideal for LWMR Laser Applications
- Aluminum and Gold Coating Options


Metal Substrate Mirrors are available with either a protected aluminum or gold coating and are ideal for LWMR (greater than 2000nm) laser applications. Due to the 17.5nm roughness of the diamond turned surface, these mirrors may not be suitable for UV and visible applications that require low scatter. The backs of the mirrors are machined flat and are tapped with 3 holes for easy, accurate mounting. Metal Substrate Mirrors are aluminum substrate, diamond turned metal mirrors. These mirrors are available in five diameters: 25.4, 38.1, 50.8, 76.2, and 101.6mm.

## Technical Information

Protected Aluminum AISiO Theoretical



Protected Gold Theoretical



## Compatible Mounts

