

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 355nm, 50mm Diameter, OD 4.0 Notch Filter



TECHSPEC OD 4.0 Notch Filters

Stock #67-124 3-4 DAYS

[Additional Bandwidths](#)



1



€904,00

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €904,00 |

|         |
|---------|
| Qty 6+  |
| €704,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
50.00 +0.00/-0.10

Optical Density OD (Average):  
≥4.0

Clear Aperture CA (mm):

|                                                                                                                                                                                     |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 42.5                                                                                                                                                                                |
| <b>Center Wavelength CWL (nm):</b><br>355.00                                                                                                                                        |
| <b>Design Wavelength DWL (nm):</b><br>355                                                                                                                                           |
| <b>Full Width-Half Max FWHM (nm):</b><br>17.80                                                                                                                                      |
| <b>Coating:</b><br>Hard Coated                                                                                                                                                      |
| <b>Surface Quality:</b><br>60-40                                                                                                                                                    |
| <b>Thickness (mm):</b><br>5.00                                                                                                                                                      |
| <b>Thickness Tolerance (mm):</b><br>±0.1                                                                                                                                            |
| <b>Transmission (%):</b><br>90                                                                                                                                                      |
| <b>Transmission Wavelength (nm):</b><br>325 - 475                                                                                                                                   |
| <b>Type:</b><br>Notch Filter                                                                                                                                                        |
| <b>Construction:</b><br>Mounted in Black Anodized Ring                                                                                                                              |
| <b>Reflection at CWL (%):</b><br>99                                                                                                                                                 |
| <b>Transmitted Wavefront, RMS:</b><br><1λ                                                                                                                                           |
| <b>Environmental Durability:</b><br>Humidity per MIL-STD-810H, Section 507.6<br>Temperature per MIL-STD-810H, Section 501.7 and 502.7                                               |
| <b>Physical Durability:</b><br>Adhesion per MIL-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11<br>Cleaning per MIL-C-48497A Section 4.5.4.2 |
| <b>Mount Thickness (mm):</b><br>5.0                                                                                                                                                 |
| <b>Substrate Thickness (mm):</b><br>3.5 ±0.5                                                                                                                                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |