

38.1mm Dia., Aluminum Coated, Aluminum Substrate Mirror



Metal Substrate Mirrors

Stock #47-115 In Stock

1 **€210,00**

ADD TO CART

Qty 1-5

€210,00

Qty 6+

€189,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
38.10 +0.00/-0.38

Substrate:
Aluminum 6061-T6

Surface Quality:
80-50

Coating Specification:
R_{avg} >85% @ 400 - 700nm
R_{avg} >70% @ 700 - 2000nm
R_{avg} >97% @ 2 - 12μm

Coating:
Protected Aluminum (400-12000nm)

Coating Type:
Metal

Clear Aperture (%):
90

Mounting Threads:
6-32 TPI Tapped Holes

Surface Roughness (□):
<175

Thickness (mm):
9.50

Type:
Flat Mirror

Wavelength Range (μm):
0.4 - 12

Wavelength Range (nm):
400 - 12000

Surface Flatness (RMS):
λ/4

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)
