

## 35mm 2 MegaPixel Fixed Focal Length Lens



35mm Fixed Focal Length, #14-400

Stock **#14-400** **2 In Stock**

⊖ 1 ⊕ €406<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€406,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

Fixed Focal Length Lens **Type:**

#### Physical & Mechanical Properties

Variable **Iris Option:**

36.91 **Length (mm):**

**Maximum Diameter (mm):**

32.5

Weight (g):

90

## Optical Properties

Horizontal Field of View @ Max Sensor Format:

14.4°

Horizontal Field of View, 2/3" Sensor:

14.4°

Horizontal Field of View, 1/2" Sensor:

10.5°

Horizontal Field of View, 1/3" Sensor:

8°

Horizontal Field of View, 1/4" Sensor:

5.23°

Maximum Image Circle (mm):

11.00

Focal Length FL (mm):

35.00

Working Distance (mm):

500 - ∞

Aperture (f/#):

f/1.4 - f/32

Distortion (%):

<-1

Lens Wavelength Range:

VIS

## Sensor

Maximum Sensor Format:

2/3"

## Threading & Mounting

Filter Thread:

M30.5 x 0.50 (Female)

Mount:

C-Mount

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Product Details

- 2 MegaPixel Resolution Design
- Lockable, Manual Focus and Iris
- Fixed Focal Lengths from 4 to 50mm
- C-Mount Lens Mount

2 MegaPixel Fixed Focal Length Lenses are designed for machine vision applications that require higher resolution than the [MegaPixel Fixed Focal Length Lenses](#). These C-Mount lenses feature built-in locking mechanisms for the manual focus and iris, preventing unwanted adjustments. Lenses with a fixed focal length from 4 to 50mm are available with the 6 to 50mm lenses featuring M30.5 x 0.5 filter thread, allowing the use of [machine vision filters](#). 2 MegaPixel Fixed Focal Length Lenses cover 1/2" and 2/3" sensor sizes, making them compatible with all of our [2MP machine vision cameras](#). These lenses are used in industrial machine vision, [factory automation](#), and factory inspection applications.