

TECHSPEC® 35mm C VIS-NIR Series Fixed Focal Length Lens



35mm Focal Length, #67-716

Stock #67-716 ☒ In Stock

⊖ 1 ⊕ **€430,00**

ADD TO CART

Qty 1+

€430,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Variable

Length (mm):
41.00

Horizontal Field of View, 1/2" Sensor:
28.5mm - 10.4°

Horizontal Field of View, 2/3" Sensor:
39.3mm - 14.3°

Filter Thread:

M25.5 x0.50 (Female)
Maximum Diameter (mm): 33
Outer Diameter (mm): 33.0
Weight (g): 75
Horizontal Field of View, 1/3" Sensor: 21.4mm - 7.8°
Maximum Rear Protrusion (mm): 0
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0559
Horizontal Field of View @ Max Sensor Format: 39.2mm - 14.2°
Number of Elements (Groups): 7 (6)
Horizontal Field of View, 1/1.8" Sensor: 32.1mm - 11.7°
Horizontal Field of View, 1/2.5" Sensor: 25.8mm - 9.4°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 35.00
Primary Magnification PMAG: 0.226
Maximum Sensor Format: 2/3"
Working Distance (mm): 165 - ∞
Mount: C-Mount
Aperture (f/#): f/1.65 - f/22
Coating: 425 - 1000nm BBAR
Coating Specification: 425 - 1000nm BBAR
Entrance Pupil Position (mm): 21.27
Horizontal Field of View, 1/4" Sensor: 16.0mm - 5.9°
Object Space Principal Plane (mm): 22.41
Image Space Principal Plane (mm): -20.66
Field of View at Max Sensor Format: Horizontal: 39.2mm - 14.3° Vertical: 29.4mm - 10.7° Diagonal: 49.1mm - 17.8°
Maximum Distortion (%): 0.17
Exit Pupil Position (mm): -21.84
Lens Wavelength Range: VIS-NIR
Imaging Lens Type: Compact Lens Coated for Visible to Near Infared
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View

