

TECHSPEC<sup>®</sup> 35mm, f/11 Cr Series Fixed Focal Length Lens



35mm Cr Series Fixed Focal Length Lens



Stock **#35-187** 2 In Stock

-

1

+

€310<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €310,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Cr Series

Product Family:

Fixed Focal Length Lens

Type:

Physical & Mechanical Properties

Iris Option:

|       |                               |
|-------|-------------------------------|
| Fixed |                               |
| 36.69 | Length (mm):                  |
| 33.8  | Maximum Diameter (mm):        |
| 33.8  | Outer Diameter (mm):          |
| 65    | Weight (g):                   |
| 3.32  | Maximum Rear Protrusion (mm): |
| 33.80 | Diameter (mm):                |

|                                                                                                                           |                                     |
|---------------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| Optical Properties                                                                                                        |                                     |
| Horizontal Field of View @ Max Sensor Format:<br>38.5mm - 14.2°                                                           |                                     |
| Field of View at Max Sensor Format:<br>Horizontal: 38.5mm - 14.3°<br>Vertical: 28.8mm - 10.8°<br>Diagonal: 48.1mm - 17.8° |                                     |
| Horizontal Field of View, 2/3" Sensor:<br>38.5mm - 14.2°                                                                  |                                     |
| Horizontal Field of View, 1/1.8" Sensor:<br>31.5mm - 11.7°                                                                |                                     |
| Horizontal Field of View, 1/2" Sensor:<br>28.0mm - 10.4°                                                                  |                                     |
| Horizontal Field of View, 1/2.5" Sensor:<br>25.4mm - 9.4°                                                                 |                                     |
| Horizontal Field of View, 1/3" Sensor:<br>21.0mm - 7.8°                                                                   |                                     |
| Horizontal Field of View, 1/4" Sensor:<br>15.7mm - 5.9°                                                                   |                                     |
| 11.00                                                                                                                     | Maximum Image Circle (mm):          |
| 0.0085                                                                                                                    | Numerical Aperture NA, Object Side: |
| 7 (6)                                                                                                                     | Number of Elements (Groups):        |
| 35.00                                                                                                                     | Focal Length FL (mm):               |
| 165 - ∞                                                                                                                   | Working Distance (mm):              |
| f/11                                                                                                                      | Aperture (f/#):                     |
| 425 - 675nm BBAR                                                                                                          | Coating:                            |
| 425 - 675nm BBAR                                                                                                          | Coating Specification:              |
| 21.27                                                                                                                     | Entrance Pupil Position (mm):       |
| 22.42                                                                                                                     | Object Space Principal Plane (mm):  |
| -20.67                                                                                                                    | Image Space Principal Plane (mm):   |
| 0.17                                                                                                                      | Maximum Distortion (%):             |
| -21.87                                                                                                                    | Exit Pupil Position (mm):           |
| VIS                                                                                                                       | Lens Wavelength Range:              |

|        |                        |
|--------|------------------------|
| Sensor |                        |
| 2/3"   | Maximum Sensor Format: |
| 2.74   | Pixel Size (µm):       |

|                      |                |
|----------------------|----------------|
| Threading & Mounting |                |
| M25.5 x0.50 (Male)   | Filter Thread: |
| M25.5 x0.5 (Male)    | Front Thread:  |

|         |        |
|---------|--------|
| C-Mount | Mount: |
|---------|--------|

Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60

Type of Ruggedization:

Stabilized (Robust Mechanics for Shock and Vibration)

Regulatory Compliance

Certificate of Conformance:

View

## Product Details

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Ruggedized (Cr) Designs (50g Shock) of our C Series Lens
- 3.5mm to 50mm Focal Length
- [Instrumentation \(Ci\) Versions](#) Also Available

TECHSPEC® Compact Ruggedized (Cr) Series Fixed Focal Length Lenses provide Stabilized Ruggedization, protecting the lens from damage while maintaining optical pointing and positioning after shock and vibration. All individual lens elements are glued in place to reduce object shift on the image. In addition, these lenses feature robust mechanics with a simplified focus and stainless steel locking C-Mount clamp. TECHSPEC® Cr Series Fixed Focal Length Lenses are ideal for calibrated imaging systems such as measurement and gauging, 3D stereo vision, robotics and sensing, autonomous vehicles, and object tracking. The object to image mapping is maintained even after heavy shock and vibration; if the center of the object maps onto the center pixel, it will always map to that same center pixel.

These lenses won the [1<sup>st</sup> place 2018 Inspect Award](#) and the [Silver Level 2018 Innovators Award](#).

**Note:** To learn more about ruggedization, visit our [Ruggedization Resource Webpage](#).

Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.

## Technical Information

Image Height vs. Distortion: 35-187, 35mm

This graph plots Image Height (mm) on the y-axis (0.55 to 5.50) against Distortion (%) on the x-axis (-0.21 to 0.21). Four curves represent different wavelengths: 656.27nm (red), 587.56nm (green), 486.13nm (blue), and an unlabeled purple curve. The curves show that distortion increases with image height and varies slightly with wavelength. The top of the y-axis is marked with sensor sizes: 2/3", 1/1.8", 1/2", and 1/2.5".

Working Distance: Infinity

#35-187, 35mm, f/11 Cr Series Fixed Focal Length Lens, Distortion Plot

Relative Illumination Plot: 35-187, 35mm

This graph plots Relative Illumination (%) on the y-axis (0 to 100) against Image Field Height (mm) on the x-axis (0.55 to 5.50). A single red line at 100% represents the f/11.0 F/Number. Vertical dashed lines indicate sensor sizes: 1/2.5", 1/2", 1/1.8", and 2/3".

Working Distance: 165.00mm      Wavelength Range: 486nm-656nm


#35-187, 35mm, f/11 Cr Series Fixed Focal Length Lens, Relative Illumination Plot

Working Distance vs. Field of View: 35-187, 35mm


This graph plots Horizontal Field of View (mm) on the y-axis (0 to 350) against Working Distance (mm) on the x-axis (165 to 1415). Five lines represent different sensor sizes: 2/3" (red), 1/1.8" (green), 1/2" (blue), 1/2.5" (purple), and 1/3" (cyan). The field of view increases linearly with working distance for each sensor size.

Wavelength Range: 486nm-656nm


#35-187, 35mm, f/11 Cr Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#35-187, 35mm, f/11 Cr Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 300mm Working Distance, f11



#35-187, 35mm, f/11 Cr Series Fixed Focal Length Lens, Depth of Field Plot, 300mm Working Distance, f11



#35-187, 35mm, f/11 Cr Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f11



#35-187, 35mm, f/11 Cr Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f11

## Compatible Cameras