

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 38.1mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock #34-816 3-4 DAYS



1



€165,00

ADD TO CART

Qty 1-5

€165,00

Qty 6+

€145,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) 90
Back Surface: Commercial Polish
Reflection at DWL (%) 99.5
Coating Specification: R_{abs} >99.5% @ 266nm R_{avg} >99.5% @ 263 - 268nm
Wavelength Range (nm): 263 - 268
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (263-268nm)
Design Wavelength DWL (nm): 266
Diameter (mm): 38.10 +0.00/-0.10
Thickness (mm): 6.35 ±0.2
Angle of Incidence (°): 45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, Reference: 2.5 J/cm² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View