

TECHSPEC®

3mm Dia. x 3mm FL, MgF₂ Coated, Double-Convex Lens



Stock **#31-858** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€55,00

ADD TO CART

Qty 1-9
€55,00
Qty 10+
€49,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Back Focal Length BFL (mm):

2.21
Effective Focal Length EFL (mm): 3.00
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-SF5
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): 30-45, typical
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.30
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.64
Radius R₁=R₂ (mm): 3.50
Clear Aperture CA (mm): 2.50
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant