

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 3mm Dia. x 9mm FL, VIS-NIR Coated, Double-Convex Lens



Stock #49-450 ☐ In Stock
[Other Coating Options](#)

1 €65,00

ADD TO CART

Qty 1-9
€65,00
Qty 10+
€58,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Back Focal Length BFL (mm):

8.46
Effective Focal Length EFL (mm): 9.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.60
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.35
Radius R₁=R₂ (mm): 9.02
Clear Aperture CA (mm): 2.5
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant