

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #38-377-INK [CONTACT US](#)

[Other Coating Options](#)



1



€53,50

ADD TO CART

Qty 1-9

€53,50

Qty 10+

€48,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.40 ±0.025

Effective Focal Length EFL (mm):

|                                                                                        |
|----------------------------------------------------------------------------------------|
| 40.00 @ 587.6nm                                                                        |
| <b>Back Focal Length BFL (mm):</b><br>36.11                                            |
| <b>Coating:</b><br>NIR I (600-1050nm)                                                  |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm                 |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                    |
| <b>Surface Quality:</b><br>40-20                                                       |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                  |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                            |
| <b>Focal Length Tolerance (%):</b><br>±1                                               |
| <b>Centering (arcmin):</b><br><1                                                       |
| <b>Center Thickness CT (mm):</b><br>5.90 ±0.10                                         |
| <b>Edge Thickness ET (mm):</b><br>1.54                                                 |
| <b>Radius R<sub>1</sub> (mm):</b><br>20.67                                             |
| <b>Clear Aperture CA (mm):</b><br>24.4                                                 |
| <b>f/#:</b><br>1.57                                                                    |
| <b>Numerical Aperture NA:</b><br>0.32                                                  |
| <b>Type:</b><br>Plano-Convex Lens                                                      |
| <b>Bevel:</b><br>Protective bevel as needed                                            |
| <b>Wavelength Range (nm):</b><br>600 - 1050                                            |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>7 J/cm² @ 1064nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |