

[See all 10 Products in Family](#)

3mm FL, f/4, Low Distortion M12 Lens



3mm FL, Low Distortion M12 Lens

Stock #75-200 NEW **1 In Stock**

⊖ 1 ⊕ €241⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€241,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

M12 Imaging Lens **Imaging Lens Type:**

Physical & Mechanical Properties

Fixed **Iris Option:**

22.28 **Length (mm):**

Maximum Diameter (mm):

16.0

Outer Diameter (mm):

16.0

Weight (g):

6

Maximum Length (mm):

22.28

Optical Properties

Horizontal Field of View @ Max Sensor Format:

76.9°

Field of View at Max Sensor Format:

Horizontal: 76.9°

Vertical: 61.6°

Diagonal: 89.6°

Focal Length FL (mm):

3.00

Working Distance (mm):

100 - ∞

Aperture (f#):

f/4

Maximum Distortion (%):

-0.02

Exit Pupil Position (mm):

-53.1

Lens Wavelength Range:

VS

Sensor

Optimized Sensor Format:

1/2.5"

Maximum Sensor Format:

1/2.5"

Threading & Mounting

Mount:

S-Mount (M12 x0.5)

Environmental & Durability Factors

Storage Temperature (°C):

-20 to +60

Regulatory Compliance

Certificate of Conformance:


[View](#)

Product Details


- Distortion as low as -0.02%
- Up to 1/1.8", S-Mount Options
- 1.7mm - 5mm Focal Lengths

Ultra Low Distortion Wide Angle Lenses are designed to achieve less than -0.02% distortion over a 76.9° field of view, less than -0.32% distortion over a 109.1° field of view, or less than -0.51% distortion over a 59.8° field of view. The ultra-low distortion values of these lenses ensure imaging with straight lines and natural object shapes, helping to reduce post-processing requirements. These lenses offer high transmission from the VS to NIR and are available in focal lengths of 1.70, 3.00, and 5.00mm. Ultra Low Distortion Wide Angle Lenses' low focal lengths allow for capturing more of the scene in a single frame. These lenses are ideal for surveillance, security, robotics, drive assistance systems, and [factory automation applications](#).


Technical Information




3mm FL, f/4, Low Distortion M12 Lens, Distortion Plot



3mm FL, f/4, Low Distortion M12 Lens, MTF Plot



3mm FL, f/4, Low Distortion M12 Lens, Relative Illumination Plot



3mm FL, f/4, Low Distortion M12 Lens, Transmission Plot