


TECHSPEC® 12.0mm Dia. x 50mm FL, YAG-BBAR, Inked, Plano-Convex Lens



YAG-BBAR Coated Plano-Convex (PCX) Lenses



Stock **#38-577-INK** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕

€54,00

ADD TO CART

Qty 1-9

€54,00

Qty 10+

€48,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 ±0.025

Effective Focal Length EFL (mm): 50.00 @ 587.6nm
Back Focal Length BFL (mm): 48.75
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.90 ±0.05
Edge Thickness ET (mm): 1.19
Radius R₁ (mm): 25.84
Clear Aperture CA (mm): 11
f/#: 4.17
Numerical Aperture NA: 0.12
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 500 - 1100
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View