

TECHSPEC® 3mm Dia. x 9mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#45-090** ☐ In Stock

☐ [Other Coating Options](#)

1

€109,00

ADD TO CART

Qty 1-5

€109,00

Qty 6+

€87,25

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Effective Focal Length EFL (mm): 9.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 7.79
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 2.7
Centering (arcmin): <3
Center Thickness CT (mm): 2.50 ±0.10
Center Thickness CT 1 (mm): 1.47 ±0.05
Center Thickness CT 2 (mm): 1.03 ±0.05
Radius R₁ (mm): 5.26
Radius R₂ (mm): -3.98
Radius R₃ (mm): -12.05
Edge Thickness ET (mm): 2.19
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 20-10
f/#: 3.00
Numerical Aperture NA: 0.17
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View