

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 405nm CWL, 12.5mm Dia., Hard Coated OD 4.0 5nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 5nm Bandpass Filters

Stock #39-330 3-4 DAYS

[Additional Bandwidths](#)



1



€213,00

ADD TO CART

Qty 1-5

€213,00

Qty 6+

€170,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Angle of Incidence (°):
0

Optical Density OD (Average):

≥4.0
Clear Aperture CA (mm): 8.5
Center Wavelength CWL (nm): 405.00 ±1.0
Full Width-Half Max FWHM (nm): 5.00 ±1.0
Substrate: ☐ Optical Glass
Minimum Transmission (%): >85
Coating: Hard Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: Diode Laser
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Mount Thickness (mm): 5.0 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant