

TECHSPEC<sup>®</sup> 3" Dia, 12" FL Uncoated, Spherical Mirror



Stock **#49-599** [CONTACT US](#)

-

1

+

€218<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €218,00 each                  |
| Qty 10-25      | €184,00 each                  |
| Qty 26-49      | €174,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spherical Mirror

Type:

Physical & Mechanical Properties

3.0

Diameter (inches):

76.20 +1.0/-0

Diameter (mm):

|          |                              |
|----------|------------------------------|
| +0.04/-0 | Diameter Tolerance (inches): |
| Ground   | Back Surface:                |
| 0.50     | Edge Thickness ET (inches):  |
| 12.70    | Edge Thickness ET (mm):      |

|          |                               |
|----------|-------------------------------|
| +0.0/-15 | Edge Thickness Tolerance (%): |
|----------|-------------------------------|

Optical Properties

|                            |                                     |
|----------------------------|-------------------------------------|
| <a href="#">BOROFLOAT®</a> | Substrate: <input type="checkbox"/> |
| ±2                         | Focal Length Tolerance (%):         |

|       |                   |
|-------|-------------------|
| 60-40 | Surface Quality:  |
| λ/4   | Surface Accuracy: |

|        |                                      |
|--------|--------------------------------------|
| 12.00  | Effective Focal Length EFL (inches): |
| 304.80 | Effective Focal Length EFL (mm):     |

|        |                           |
|--------|---------------------------|
| 609.60 | Radius of Curvature (mm): |
| f/4    | Aperture (f/#):           |

|          |               |
|----------|---------------|
| Uncoated | Coating:      |
| Uncoated | Coating Type: |

Regulatory Compliance


|                      |                             |
|----------------------|-----------------------------|
| <a href="#">View</a> | Certificate of Conformance: |
|----------------------|-----------------------------|

## Product Details

- Ideal for Multispectral Focusing Applications
- Variety of Coating Options Offered
- Multiple Sizes Available
- [λ/8 Precision Spherical Mirrors](#) Also Available

TECHSPEC® λ/4 Precision Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors are available in a wide range of metallic coating options covering the UV, VIS, and IR spectrum. A BOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® λ/4 Precision Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors collect and focus light without introducing chromatic aberration.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

