

TECHSPEC® 40.0mm Dia. x 200.0mm FL, NIR I Coated, Plano-Convex Lens



Stock **#33-380** 3-4 DAYS

[Other Coating Options](#)

− 1 + **€59,00**

ADD TO CART

Qty 1-9
€59,00
Qty 10+
€53,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):

200.00 @587.6nm
Back Focal Length BFL (mm): 196.7
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.10
Edge Thickness ET (mm): 3.05
Radius R₁ (mm): 103.36
Clear Aperture CA (mm): 39
f/#: 5
Numerical Aperture NA: 0.10
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant