

TECHSPEC® 40mm Dia. x 120mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-381-INK** 3-5 DAYS
[Other Coating Options](#)

⊖ 1 ⊕ **€190,00**

ADD TO CART

Qty 1-5
€190,00
Qty 6+
€152,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 ±0.025

Effective Focal Length EFL (mm):

120.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 111.00
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 39.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 13.80 ±0.20
Center Thickness CT 1 (mm) : 9.6 ±0.10
Center Thickness CT 2 (mm) : 4.2 ±0.10
Radius R₁ (mm) : 65.22
Radius R₂ (mm) : -62.03
Radius R₃ (mm) : -1240.67
Edge Thickness ET (mm) : 10.51
Substrate:  N-SSK8 / N-SF10
Surface Quality : 40-20
f/# : 3.00
Numerical Aperture NA : 0.17
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View