

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 40mm Dia. X 40mm FL, NIR II Coated, Double-Convex Lens



Stock #67-666-INK [CONTACT US](#)

[Other Coating Options](#)

1 **€72,50**

ADD TO CART

Qty 1-9
€72,50

Qty 10+
€65,25

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 ±0.025

Back Focal Length BFL (mm):

37.54
Effective Focal Length EFL (mm): 40.00
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 8.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.74
Radius R ₁ =R ₂ (mm): 60.85
Clear Aperture CA (mm): 39.00
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View