

TECHSPEC®

40mm Dia., 0.80 Numerical Aperture, 900-1700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#17-010-INK** [CONTACT US](#)

[Other Coating Options](#)



1



€645,00

ADD TO CART

Qty 1-5

€645,00

Qty 6+

€516,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
40.00 ±0.025

Effective Focal Length EFL (mm):

25.00 @ 587.6nm
Numerical Aperture NA: 0.80
Back Focal Length BFL (mm): 17.74
Substrate: □ N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: SWR+ (900-1700nm)
Coating Specification: R _{avg} <0.5% @ 900 - 1700nm @ ±30° AOI R _{abs} <1.5% @ 900 - 1700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 36.00
Edge Thickness ET (mm): 2.40
Center Thickness CT (mm): 13.10 ±0.10
f#: 0.63
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 900 - 1700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View