

TECHSPEC[®] 40mm Dia. 320 - 450nm Broadband λ /10 Mirror



Stock **#37-570** [CONTACT US](#)

-

1

+

€254⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€254,00 each
Qty 6-25	€203,00 each
Qty 26-49	€190,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Flat Mirror

Physical & Mechanical Properties

Diameter (mm):

40.00 +0.00/-0.20	
5.00 ±0.20	Thickness (mm):
Commercial Polish	Back Surface:
90	Clear Aperture (%):
Ground, 0.5mm max bevel	Edges:
<0.5	Parallelism (arcmin):


Optical Properties	
Dielectric	Coating Type:
Dielectric Mirror (320-450nm)	Coating:
λ/10	Surface Flatness (P-V):
320 - 450	Wavelength Range (nm):
Fused Silica (Corning 7980)	Substrate: □
0-45	Angle of Incidence (°):
Coating Specification: R _{avg} >98% @ 340 - 488nm (0°, All Polarizations) R _{avg} >98% @ 320 - 450nm (45°, All Polarizations) R _{avg} >99% @ 320 - 450nm (45°, S-Polarization)	
20-10	Surface Quality:
Damage Threshold, By Design: □ 0.5 J/cm ² @ 355nm, 20ns, 20Hz	

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

- Enhanced Reflectivity and LIDT over Metallic Coatings
 - Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
 - Designed for all Polarization States from 0 – 45° AOI
- TECHSPEC® Broadband Dielectric λ/10 Mirrors are ideal for beam steering or reflection applications utilizing multiple laser sources. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. The highly durable fused silica substrate offers a low thermal expansion coefficient and a high abrasion resistance. TECHSPEC® Broadband Dielectric λ/10 Mirrors are designed for applications from the UV to the near-infrared spectra.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

;