

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Hard Coated OD5 Bandpass Filters](#)

[See all 52 Products in Family](#)

430nm CWL, >0

25mm Dia.

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Hard Coated OD5 Bandpass Filters

1

€205^{.00}

ADD TO CART

Volume Pricing	
Qty	€205,00
1+	each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
eDrawing:eprt	
EO Spec Sheet	Download All

Prices shown are exclusive of VAT/local taxes

General

Type:	Bandpass Filter	Typical Applications:	Scattered light and point detection (Flow Cytometry), not suitable for imaging, immunophenotyping
Note:	Arrow on ring indicates preferred direction of propagation of light.		

Physical & Mechanical Properties

Diameter (mm):	25.00 ±0.10	Clear Aperture CA (mm):	>22
Construction:	Mounted in Black Anodized Ring	Substrate Thickness (mm):	2.00 ±0.10

Optical Properties

Angle of Incidence (°):	0 ±5	Bandwidth (nm):	16
Optical Density OD (Average):	>5	Center Wavelength CWL (nm):	430.00 (Nominal)
Full Width-Half Max FWHM (nm):	20.00 (Nominal)	Substrate:	Optical Grade Glass
Minimum Transmission (%):	>93 @ 422 – 438nm	Coating:	Hard Coated
Surface Quality:	80-50	Blocking Wavelength Range (nm):	330 - 900
Cone Half Angle (°):	7		

Threading & Mounting

Mount Thickness (mm): 3.50 ±0.10

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Regulatory Compliance

RoHS 2015: **Compliant**

Reach 253: **Compliant**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Suitable for Single-Point Fluorescence Detection and Flow Cytometry Applications
- 52 Distinct Design Wavelengths Covering the NUV – NIR Spectrum
- >OD5 Average Blocking from 330 – 900nm
- Mounted for Easy Handling and System Integration

Hard Coated OD5 Bandpass Filters are available in 52 distinct passbands with design wavelengths from 340 to 895nm in step increments of 10–15nm in the NUV, VIS, and NIR. These cost-efficient hard-coated filters feature high transmission (>90%) with full-width half maximum (FWHM) of 20nm, or 30nm in the NIR, for essential optical performance. Hard Coated OD5 Bandpass Filters feature high average blocking >OD5 outside the passband from 330 – 900nm, making them suited for flow cytometry and single-point fluorescence detection, such as photometry and point-scanning. All filters are mounted in 25mm diameter black anodized aluminum rings to facilitate handling and system integration.

Related Products



#64-561 – 25.4mm Optic Dia.,
10mm Max Optic Thickness,
Optic Mount
€32,75

Qty



Hard Coated OD 4.0 25nm
Bandpass Filters

Frequently Purchased Together



Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

25mm Dia.
€205,00

 