

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #18-387 □ In Stock

[□ Additional Bandwidths](#)



1



€312,00

ADD TO CART

Qty 1-5

€312,00

Qty 6+

€261,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 ±0.1

Angle of Incidence (°):
0 ±5

Bandwidth (nm): 20.00
OD 6 Blocking Wavelength Range (nm): 250 - 423 & 471 - 950
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 22.50
Center Wavelength CWL (nm): 448.00
Full Width-Half Max FWHM (nm): 25.00
Substrate: ☐ Fused Silica (Coming 7980)
Minimum Transmission (%): 93
Coating: Hard Coated
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.1
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 - 1100
Construction: Unmounted
Transmitted Wavefront, RMS: λ/4 (prior to coating)
Compatible Fluorophore: 442nm Laser Excitation
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Bevel: Protective bevel as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant