


45° Fan Angle, 400 - 500nm AR Coated, High Precision Powell Lens



Stock **#70-133** 1 In Stock

-

1

+

€316^{,21}

ADD TO CART

Volume Pricing	
Qty 1-10	€316,21 each
Qty 11-49	€284,28 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Beam Shaping Lens

Type:

Physical & Mechanical Properties

8.90 +0.00/-0.15	Dimensions (mm):
8.90 +0.00/-2.00	Height (mm):
1.3	Input Beam Diameter, 1/e ² (mm):
Optical Properties	
N-SF6	Substrate: □
BBAR (400-500nm)	Coating:
400 - 500	Wavelength Range (nm):
R _{abs} <1.0% @ 400 - 500nm	Coating Specification:
1.458	Index of Refraction (n _d):
45.00	Fan Angle (°):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Generate Uniform, Flat-Top Profile Over Entire Line
- Fan Angles from 1° to 75° Available
- AR Coated for 400 - 500nm or 500 - 850nm

Precision Powell Lenses, also known as aspheric line generators (ALGs), spread an input beam across a uniform line with a top-hat beam profile at a specified fan angle. These Powell lenses are produced through a precision manufacturing process to ensure high contained power, uniformity, and line straightness across the entire produced line, as well as superior part-to-part consistency. They are designed for a specific input beam diameter to provide best line uniformity; larger input beams will result in higher intensity at the ends of the generated line, while smaller will create a more Gaussian distribution. Precision Powell Lenses are ideal for use in machine vision and life science applications including 3D profile measurement, PCB inspection, line-scan SD-OCT, line-scan confocal microscopy, flow cytometry, and particle analysis.