

A black cylindrical device, likely a sensor or probe, is shown against a dark background. A green fiber optic cable is connected to the side of the cylinder. The cable has a green protective sheath and a metal connector. The device is positioned diagonally, and the cable extends from its side.

⊖ 1 ⊕ €1.400^{,00}

[ADD TO CART](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

General	
1	General
2	General
3	General
4	General
5	General
6	General
7	General
8	General
9	General
10	General
11	General
12	General
13	General
14	General
15	General
16	General
17	General
18	General
19	General
20	General
21	General
22	General
23	General
24	General
25	General
26	General
27	General
28	General
29	General
30	General
31	General
32	General
33	General
34	General
35	General
36	General
37	General
38	General
39	General
40	General
41	General
42	General
43	General
44	General
45	General
46	General
47	General
48	General
49	General
50	General
51	General
52	General
53	General
54	General
55	General
56	General
57	General
58	General
59	General
60	General
61	General
62	General
63	General
64	General
65	General
66	General
67	General
68	General
69	General
70	General
71	General
72	General
73	General
74	General
75	General
76	General
77	General
78	General
79	General
80	General
81	General
82	General
83	General
84	General
85	General
86	General
87	General
88	General
89	General
90	General
91	General
92	General
93	General
94	General
95	General
96	General
97	General
98	General
99	General
100	General

Type of Laser:

IIIb	Laser Class - CDRH:
Physical & Mechanical Properties	
1	Length of Fiber (m):
Optical Properties	
0.12	Numerical Aperture NA:
Fiber-Coupled	Spatial Mode:
3	Fiber Diameter (μm):
460.00 ±10	Wavelength (nm):
Blue	Color:
Electrical	
30	Output Power (mW):
Hardware & Interface Connectivity	
5.0	Operating Voltage (V):
Power Supply: Power Supply Required and Sold Separately: USA: #73-818 Europe: #73-818 Japan: #13-640 Korea: #33-770 China: #73-818	
FC/PC	Connector:
Environmental & Durability Factors	
+15 to +30	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- Single Mode Fiber with FC/PC Connector
 - 1 to 100mW Output Power and 405 to 1550nm Wavelength Options
 - Integrated Driver for Easy Operation
- Pigtailed Laser Diode Modules feature an integrated 1m long, single mode fiber with an FC/PC connector. These laser diodes also feature an integrated driver for plug and play operation, only requiring a 5V external power supply ([#73-818](#)). Pigtailed Laser Diode Modules are available with VIS and NIR wavelengths ranging from 405 to 1550nm, with output powers ranging from 1 to 100mW. Their plug and play operation make these laser diodes ideal for a wide range of laboratory and OEM applications.