

TECHSPEC® 40mm Dia. x 750mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#67-336-INK** [CONTACT US](#)
[Other Coating Options](#)

- 1 + **€190,00**

ADD TO CART

Qty 1-5
€190,00
Qty 6+
€152,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
40.00 ±0.025

Effective Focal Length EFL (mm):

750.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 744.37
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 39.00
Centering (arcmin): <1
Center Thickness CT (mm): 8.00 ±0.20
Center Thickness CT 1 (mm): 4.00 ±0.10
Center Thickness CT 2 (mm): 4.00 ±0.10
Radius R ₁ (mm): 315.18
Radius R ₂ (mm): -506.69
Radius R ₃ (mm): -∞
Edge Thickness ET (mm): 7.36
Substrate:  N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 18.75
Numerical Aperture NA: 0.03
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View