

TECHSPEC[®] 488nm CWL, 25mm Dia, 1.9nm Bandwidth, OD 6 Laser Line Bandpass Filter



Stock **#68-967** 3-4 DAYS
[Additional Bandwidths](#)

-

1

+

€692^{.00}

ADD TO CART

Qty 1-9
€692,00
Qty 10+
€608,00
Volume Pricing
Request Quote
! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Bandpass Filter

Physical & Mechanical Properties	
25.00	Diameter (mm):
21.00	Clear Aperture CA (mm):
+0.0/-0.1	Thickness Tolerance (mm):
Optical Properties	
0 ±2	Angle of Incidence (°):
1.9	Bandwidth (nm):
OD 5 Blocking Wavelength Range (nm) : 415.1 - 483.1 & 492.9 - 625.3	
OD 6 Blocking Wavelength Range (nm): 449 - 480.7 & 495.3 - 536.8	
≥6.0	Optical Density OD (Average):
488.00	Center Wavelength CWL (nm):
488	Design Wavelength DWL (nm):
3.40	Full Width-Half Max FWHM (nm):
Fused Silica (Corning 7980)	Substrate: ☐
Hard Coated	Coating:
60-40	Surface Quality:
≥90	Transmission (%):
N/4 @ 633nm	Transmitted Wavefront, RMS:

Threading & Mounting	
3.5	Mount Thickness (mm):

Environmental & Durability Factors	
Durability: Environmental: ML-STD-810F, sect. 507.4 Durability: ML-C-48497A, sect. 3.4.1	




Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

PRODUCT DETAILS

- Over 90% Transmission at Design Wavelength
 - Hard Coated Design
 - Designed for Laser Applications
- Available for use with common gas and solid state lasers, TECHSPEC OD 6 Laser Line Clean-Up Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. TECHSPEC OD 6 Laser Line Clean-Up Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, TECHSPEC Laser Line Clean-Up Filters are excellent complements to [TECHSPEC Notch Filters](#) or [TECHSPEC Raman Longpass Edge Filters](#).



TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS