

TECHSPEC® 4mm Aperture x 50mm L, VIS-NIR Coated, Standard NA, Fused Silica Light Pipe



Fused Silica Light Pipe Homogenizing Rods



Stock **#23-494** 3-4 DAYS



1



€212,50

ADD TO CART

Qty 1-5

€212,50

Qty 6+

€170,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS-NIR (400-1000nm)

Substrate:

[Fused Silica](#) (Corning 7980)

Length (mm): 50.00
Surface Quality: 60-40
Type: Light Pipe
Entrance and Exit Aperture (mm): 4.00
Parallelism (arcmin): 5.00
Length Tolerance (mm): ±0.3
Aperture Tolerance (mm): ±0.10
Image Orientation: Light Homogenization
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Light Source NA: Standard
Wavelength Range (nm): 400 - 1000
Surface Flatness (P-V): 1λ
Damage Threshold, Reference:  5 J/cm² @ 532nm, 10ns
#Sorting: 24.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant