


4.50µm, 50mm Diameter, Infrared Longpass Filter



Infrared (IR) Longpass Filters

Stock **#68-661** 3-4 DAYS



1



€495,00

ADD TO CART

Qty 1-9

€495,00

Qty 10+

€445,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Optical Density OD (Average):
≥3.0

Cut-On Wavelength (nm):
4,500.00

Substrate: Germanium (Ge)
Operating Temperature (°C): -62 to +71
Coating: Traditional Coated
Surface Quality: 80-50
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.2
Transmission (%): >85
Transmission Wavelength (nm): 4730 - 9000
Transmission Wavelength (µm): 4.73 - 9.00
Type: Longpass Filter
Blocking Wavelength Range (nm): 200 - 4500
Parallelism (arcmin): <10
Clear Aperture (%): 90
Slope Factor (%): <7
Cut-On Wavelength (µm): 4.50 ±0.18
Note: Transmission at cut-on wavelength is 5% of peak transmission.
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant