

4mW 635nm Circular, Premier Laser Diode



Stock **#57-106** 8 In Stock

-

1

+

€263^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	€263,00 each
Qty 10+	€250,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

3R

Laser Class - IEC:

>15,000

Mean Time To Failures MTTF@ 25° (hours):

Includes: Users Manual, Warning Label, Wire Harness, and Focus Key

Note:

Diode	Type of Laser:
IIla	Laser Class - CDRH:
Physical & Mechanical Properties	
<0.01	Pointing Stability after Warm Up (mrad/°C):
≤10 at Factory Set Focus	Pointing Accuracy (mrad):
47.00	Length (mm):
Optical Properties	
639.00	Wavelength (nm):
±10	Wavelength Tolerance (nm):
0.25	Wavelength Stability (nm/°C):
<50	Beam Size at Nearest Focus (µm):
2.00 at Aperture	Beam Diameter (mm):
0.35 Typical	Beam Divergence (mrad):
Red	Color:
25mm - ∞	Focus Range (mm):
Electrical	
≤100	Operating Current (mA):
4	Output Power (mW):
<2	Power Stability (%):
±5	Output Power Tolerance (%):
DC to 300kHz (at 95% modulation depth to -3dB)	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
5 DC ±5%	Operating Voltage (V):
Power Supply Required and Sold Separately. USA: #59-099 Europe: Not Available Japan: #59-099 Korea: Not Available China: #59-099	Power Supply:
red (+V), black (-), yellow (Vcontrol), green/yellow (case)	Electrical Leads/ Pin Connections:
Free Space	Output Type:
Environmental & Durability Factors	
-10 to +45	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Stable Output
- True On/Off Pulsed Control
- Linear Amplitude or Time Modulation

- Low Power Consumption
- EMC/ESD Shielded
- Focusable

Premier Laser Diode Modules use advanced circuits and components to eliminate unwanted variations in output. A single input allows the light intensity to be set using a simple resistor or voltage source. The output can be modulated rapidly with any arbitrary waveform. Premier Laser Diode Modules contain an industrial quality laser diode with built-in monitoring photodiode. An efficient processor-controlled driver circuit is fully protected and matched to the diode. The stable, adjustable focus lens mounting and case is electrically isolated from the electronics. A 4-way connector provides supply, control, and shielding inputs. The modules meet IEC60825 certification, in accordance with CDRH. Applications for these laser modules include vision systems, telemetry, sensors, laboratory testing, and dynamic lighting.

A power supply, sold separately, is required for operation.
