


TECHSPEC[®] 45° AOI, 25.0mm Square, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock **#64-448** 20+ In Stock

-

1

+

€60⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€60,00 each
Qty 10-25	€54,00 each
Qty 26-49	€51,50 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Cold Mirror

Physical & Mechanical Properties

Dimensions (mm):

25.0 x 25.0


Thickness (mm):

3.30 ±0.2	
+0.0/-0.2	
Dimensional Tolerance (mm):	
Optical Properties	
Angle of Incidence (°):	
45	
Coating:	
Cold Mirror, 45°	
Substrate: ☐	
BOROFLOAT®	
Surface Quality:	
80-50	
Transmission (%):	
Dichroic Filter	
Coating Specification:	
R _{avg} ≥95% @400 - 690nm and T _{avg} ≥90% @750 - 1200nm	
AR Coating: R _{avg} <1% @700 - 1150nm	
Wavelength Range (nm):	
425 - 1150	
Surface Flatness (P-V):	
4 - 6λ	
Coating Type:	
Dielectric	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	

Product Details

- >95% Reflection from 400 - 690nm
 - >90% Transmission from 750 - 1200nm
 - Optimized for 0° or 45° Angle of Incidence
- TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

Technical Information



Quote Your Size

Compatible Mounts