

4.5mW 655nm Circular, Premier Laser Diode



Stock #57-108 **5 In Stock**

- 1 + €263^{.00}

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-9 | €263,00 each |
| Qty 10+ | €250,00 each |
| Need More? | Request Quote |

i Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

3R **Laser Class - IEC:**

Mean Time To Failures MTTF@25° (hours):
>100,000

Note:

Includes: Users Manual, Warning Label, Wire Harness, and Focus Key

| | |
|---|---|
| Diode | Type of Laser: |
| IIIa | Laser Class - CDRH: |
| Physical & Mechanical Properties | |
| <0.01 | Pointing Stability after Warm Up (mrad°C): |
| ≤10 at Factory Set Focus | Pointing Accuracy (mrad): |
| 47.00 | Length (mm): |
| Optical Properties | |
| 655.00 | Wavelength (nm): |
| ±10 | Wavelength Tolerance (nm): |
| 0.25 | Wavelength Stability (nm/°C): |
| <50 | Beam Size at Nearest Focus (µm): |
| 2.00 at Aperture | Beam Diameter (mm): |
| 0.35 Typical | Beam Divergence (mrad): |
| Red | Color: |
| 20mm - ∞ | Focus Range (mm): |
| Electrical | |
| ≤120 | Operating Current (mA): |
| 4.5 | Output Power (mW): |
| <2 | Power Stability (%): |
| ±5 | Output Power Tolerance (%): |
| DC to 300kHz (at 95% modulation depth to -3dB) | Modulation Frequency (kHz): |
| Hardware & Interface Connectivity | |
| 5 DC ±5% | Operating Voltage (V): |
| Power Supply: Power Supply Required and Sold Separately: USA: #59-099 Europe: Not Available Japan: #59-099 Korea: Not Available China: #59-099 | |
| red (+V), black (-), yellow (Vcontrol), green/yellow (case) | Electrical Leads/ Pin Connections: |
| Free Space | Output Type: |
| Environmental & Durability Factors | |
| -10 to +55 | Operating Temperature (°C): |
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 240: |

Product Details

- Stable Output
- True On/Off Pulsed Control
- Linear Amplitude or Time Modulation

- Low Power Consumption
- EMC/ESD Shielded
- Focusable

Premier Laser Diode Modules use advanced circuits and components to eliminate unwanted variations in output. A single input allows the light intensity to be set using a simple resistor or voltage source. The output can be modulated rapidly with any arbitrary waveform. Premier Laser Diode Modules contain an industrial quality laser diode with built-in monitoring photodiode. An efficient processor-controlled driver circuit is fully protected and matched to the diode. The stable, adjustable focus lens mounting and case is electrically isolated from the electronics. A 4-way connector provides supply, control, and shielding inputs. The modules meet IEC60825 certification, in accordance with CDRH. Applications for these laser modules include vision systems, telemetry, sensors, laboratory testing, and dynamic lighting.

A power supply, sold separately, is required for operation.
