


LightPath 356785 | 2.75mm Dia., 0.62 NA, BBAR (350-600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock **#83-679** CLEARANCE CONTACT US

- 1 + **€43,95**

ADD TO CART

Qty 1+
€43,95

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
2.75 ±0.015

Effective Focal Length EFL (mm):
1.42 @488nm

Numerical Aperture NA:
0.62

Substrate:

[L-LAL12](#)

Aspheric Design Wavelength (nm):
488

Coating:
BBAR (350-600nm)

Coating Specification:
R_{abs} <1.0% @ 350 - 600nm

Surface Quality:
20-10

Clear Aperture CA (mm):
1.70

Edge Thickness ET (mm):
0.6

Center Thickness CT (mm):
1.08 ±0.05

f#:
0.81

Bevel:
Protective bevel as needed

Lightpath Lens Code:
356785

Type:
Aspheric Lens

Wavelength Range (nm):
350 - 600

Working Distance (mm):
0.86

Conjugate Distance:
Infinite

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
