

TECHSPEC[®] 4mm Dia. 266nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC[®] Nd:YAG Laser Line Mirrors



Stock #12-623 14 In Stock

-

1

+

€119⁴⁸

ADD TO CART

Volume Pricing	
Qty 1-5	€119,48 each
Qty 6-25	€106,09 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Laser Mirror	
Physical & Mechanical Properties	
Parallelism (arcmin):	<3
Clear Aperture (%):	90
Back Surface:	Commercial Polish
Diameter (mm):	4.00 +0.00/-0.10
Thickness (mm):	3.00 ±0.20
Optical Properties	
Surface Quality:	10-5
Reflection at DWL (%):	99.8
Coating Specification:	R _{abs} >99.8% @ 266nm
Wavelength Range (nm):	263 - 268
Surface Flatness (P-V):	λ/10
Coating Type:	Dielectric
Coating:	Laser Mirror (266nm)
Design Wavelength DWL (nm):	266
Angle of Incidence (°):	0-45
Substrate:	Fused Silica (Corning 7980)
Damage Threshold, Reference:	2 J/cm ² @ 266nm, 20ns, 20Hz
Regulatory Compliance	
Certificate of Conformance:	View

PRODUCT DETAILS

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
 - High Laser Induced Damage Threshold Specifications
 - 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
 - [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available
- TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

COMPATIBLE MOUNTS