

TECHSPEC® 4X, NIR Vega® Broadband Beam Expander



TECHSPEC® Vega™ Broadband Beam Expanders

Stock #19-407 3-4 DAYS



1



€424,00

ADD TO CART

Qty 1+

€424,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser NIR (1030-1550nm)

Design Wavelength DWL (nm):
Broadband

Entrance Aperture (mm):
7.5

Exit Aperture (mm): 26
Expansion Power: 4X
Substrate: Fused Silica
Length (mm): 92.60
Mounting Threads: Input: Male M30 x 1 Output: Female M34 x 0.5
Transmission (%): >95.0 (nominal)
Type: Beam Expander
Weight (g): 160
Housing Diameter (mm): 39.95
Transmitted Wavefront, P-V: λ/10 for 4.0mm input beam (nominal, λ = DWL)
Coating Specification: Ravg ≤0.7% @ 1030 - 1550nm @ 0° AOI
Wavelength Range (nm): 1030 - 1550
Style: Fixed Magnification
Damage Threshold, By Design: 2 J/cm² @ 1064nm, 20ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View