

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 500nm CWL, 50mm Dia, 24nm Bandwidth, OD 6 Fluorescence Filter



Stock #67-043 3-4 DAYS

[Additional Bandwidths](#)



1



€848,00

ADD TO CART

Qty 1-5

€848,00

Qty 6+

€697,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
50.00 +0.00/-0.10

Angle of Incidence (°):  
0 ±5

Bandwidth (nm):

|                                                                                                                                                                                     |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 24.00                                                                                                                                                                               |
| <b>OD 6 Blocking Wavelength Range (nm):</b><br>250 - 473 & 525 - 670                                                                                                                |
| <b>Optical Density OD (Average):</b><br>≥6.0                                                                                                                                        |
| <b>Clear Aperture CA (mm):</b><br>45.21                                                                                                                                             |
| <b>Center Wavelength CWL (nm):</b><br>500.00                                                                                                                                        |
| <b>Full Width-Half Max FWHM (nm):</b><br>29.00                                                                                                                                      |
| <b>Substrate:</b> <br><a href="#">Fused Silica</a> (Corning 7980)                                  |
| <b>Minimum Transmission (%):</b><br>93                                                                                                                                              |
| <b>Coating:</b><br>Hard Coated                                                                                                                                                      |
| <b>Surface Quality:</b><br>60-40                                                                                                                                                    |
| <b>Thickness Tolerance (mm):</b><br>±0.1                                                                                                                                            |
| <b>Transmission (%):</b><br>93.00                                                                                                                                                   |
| <b>Type:</b><br>Bandpass Filter                                                                                                                                                     |
| <b>Blocking Wavelength Range (nm):</b><br>250 - 1100                                                                                                                                |
| <b>Construction:</b><br>Mounted in Black Anodized Ring                                                                                                                              |
| <b>Transmitted Wavefront, RMS:</b><br>λ/4 (prior to coating)                                                                                                                        |
| <b>Compatible Fluorophore:</b><br>YFP Excitation                                                                                                                                    |
| <b>Environmental Durability:</b><br>Humidity per MIL-STD-810H, Section 507.6<br>Temperature per MIL-STD-810H, Section 501.7 and 502.7                                               |
| <b>Physical Durability:</b><br>Adhesion per MIL-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11<br>Cleaning per MIL-C-48497A Section 4.5.4.2 |
| <b>Mount Thickness (mm):</b><br>3.5 ±0.1                                                                                                                                            |
| <b>Substrate Thickness (mm):</b><br>2.00 ±0.25                                                                                                                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |