

[See all 423 Products in Family](#)

TECHSPEC<sup>®</sup> 50.0mm Dia. x 500.0mm FL, NIR II Coated, Plano-Convex Lens



Stock **#67-589** 1 In Stock

☐ [Other Coating Options](#)

-

1

+

€70<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | €70,00 each                   |
| Qty 10-24      | €63,50 each                   |
| Qty 25-49      | €56,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                          |       |
|----------------------------------|-------|
| Plano-Convex Lens                | Type: |
| Physical & Mechanical Properties |       |

|                      |                           |
|----------------------|---------------------------|
| 50.00 +0.0/-0.025    | Diameter (mm):            |
| <1                   | Centering (arcmin):       |
| 5.00 ±0.10           | Center Thickness CT (mm): |
| 3.79                 | Edge Thickness ET (mm):   |
| 49                   | Clear Aperture CA (mm):   |
| Protective as needed | Bevel:                    |

Optical Properties

|                                                                                                                        |                                  |
|------------------------------------------------------------------------------------------------------------------------|----------------------------------|
| 500.00 @ 587.6nm                                                                                                       | Effective Focal Length EFL (mm): |
| 496.70                                                                                                                 | Back Focal Length BFL (mm):      |
| NIR II (750-1550nm)                                                                                                    | Coating:                         |
| R <sub>abs</sub> ≤1.5% @ 750 - 800nm<br>R <sub>abs</sub> ≤1.0% @ 800 - 1550nm<br>R <sub>avg</sub> ≤0.7% @ 750 - 1550nm | Coating Specification:           |
| N-BK7                                                                                                                  | Substrate: □                     |
| 40-20                                                                                                                  | Surface Quality:                 |
| 1.5λ                                                                                                                   | Power (P-V) @ 632.8nm:           |
| λ/4                                                                                                                    | Irregularity (P-V) @ 632.8nm:    |
| ±1                                                                                                                     | Focal Length Tolerance (%):      |
| 258.40                                                                                                                 | Radius R <sub>1</sub> (mm):      |
| 10                                                                                                                     | f/#:                             |
| 0.05                                                                                                                   | Numerical Aperture NA:           |
| 750 - 1550                                                                                                             | Wavelength Range (nm):           |
| 8 J/cm² @ 1064nm, 10ns                                                                                                 | Damage Threshold, Reference: □   |

Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| View      | Certificate of Conformance: |
| Compliant | Reach 235:                  |

## Product Details

- AR Coated to Provide <0.7% Reflectance per Surface for 750 - 1550nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [VIS-EXT](#), and [YAG-BBAR](#)


TECHSPEC® NIR II Coated Plano-Convex Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® NIR II Coated Plano-Convex Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [VIS-EXT](#), and [YAG-BBAR](#).

## Technical Information



N-BK7


Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 0.25\% @ 880\text{nm}$   
 $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$   
 $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---