

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50mm Dia., 1mm Thick, UV-AR Coated N/10 Fused Silica Window



Stock #36-938 3-4 DAYS



1



€260,00

ADD TO CART

Qty 1-5

€260,00

Qty 6+

€208,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
67.8

Bevel:
Protective as needed

Clear Aperture (%):
80

Clear Aperture CA (mm): 40.00
Diameter (mm): 50.00 +0.00/-0.20
Thickness (mm): 1.00 ±0.10
Coating: UV-AR (250-425nm)
Coating Specification: R _{abs} ≤1.0% @ 250 - 425nm R _{avg} ≤0.75% @ 250 - 425nm R _{avg} ≤0.5% @ 370 - 420nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Edges: Fine Ground
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcsec): <5
Poisson's Ratio: 0.16
Substrate: Fused Silica (Corning 7980)
Surface Quality: 20-10
Transmitted Wavefront, P-V: λ/10
Type: Protective Window
Wavelength Range (nm): 250 - 450
Young's Modulus (GPa): 73
Damage Threshold, Reference: ☐ 3 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant