

[See all 130 Products in Family](#)

TECHSPEC[®] 50mm Dia. 532nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC[®] Nd:YAG Laser Line Mirrors



Stock **#47-157** 20+ In Stock

-

1

+

€265⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€265,00 each
Qty 6-25	€235,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Laser Mirror

Physical & Mechanical Properties

Parallelism (arcmin):

<3

>90	Clear Aperture (%)
Ground	Back Surface
50.00 +0.00/-0.20	Diameter (mm)
10.00 ±0.20	Thickness (mm)
Optical Properties	
10-5	Surface Quality
99.8	Reflection at DWL (%)
Coating Specification: R _{abs} >99.8% @ 532nm @45° AOI R _{avg} >99.5% @ 523 - 537nm @45° AOI	
523 - 537	Wavelength Range (nm)
λ/10	Surface Flatness (P-V)
Dielectric	Coating Type
Laser Mirror (532nm)	Coating
532	Design Wavelength DWL (nm)
45	Angle of Incidence (°)
Fused Silica (Corning 7980)	Substrate: □
15 J/cm² @ 532nm, 20ns, 20Hz	Damage Threshold, Reference: □

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
 - High Laser Induced Damage Threshold Specifications
 - 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
 - TECHSPEC® Laser Mirror Substrates and TECHSPEC® Yb:YAG Laser Line Mirrors Also Available
- TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts