


50mm Dia., 80° Diffusion Angle, High Efficiency Diffuser



HE Single Sided Diffuser

Stock #70-768

3-4 DAYS

-

1

+

€95⁰⁰

ADD TO CART

Qty 1-9
€95,00
Qty 10+
€66,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

High Efficiency Diffuser

Type:




Physical & Mechanical Properties	
50.00 ±0.13	Diameter (mm):
1.59 +/-0.16	Thickness (mm):
Optical Properties	
80	Diffusing Angle (°):
PMMA	Substrate:
Environmental & Durability Factors	
-34 to +70	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS:
View	Certificate of Conformance:

PRODUCT DETAILS

- High Efficiency, Angle Bending, Batwing, and Elliptical Configurations Available
- Transmission Efficiency>88%
- Low-Cost, High-Performance Diffusers

Beam Shaping Diffusers provide an even distribution of LED and fluorescent illumination in a variety of configurations including High Efficiency, Angle Bending, Batwing, and Elliptical while maintaining a high transmission efficiency of >88%. The high efficiency and angle bending configurations provide even light distribution whereas the batwing and elliptical configurations distribute light according to their respective geometries. Beam Shaping Diffusers feature diffusing angles between 8° - 127° and are available as 25mm diameter unmounted optics with a thickness of no more than 1.75mm, enabling easy integration into a variety of bench top or OEM applications. These Diffusers are ideal for applications where excellent depixelation, angle control, color mixing, and color uniformity are required.

TECHNICAL INFORMATION

Type of Diffuser	Description	Diffusion Example
High Efficiency Diffuser	High Efficiency Diffusers are ideal for providing even illumination in LED applications. They provide excellent depixelation, angle control, and color uniformity.	
Linear Batwing Diffuser	Linear Batwing Diffusers diffuse light in a batwing distribution, ideal for eliminating central hotspots from a light source. Incident light should be from the glossy, specularly-reflective side of these diffusers for optimal performance. Light distributions may vary significantly depending on the light source used.	
Elliptical Diffuser	Elliptical Diffusers diffuse light assymmetrically, creating an elliptical light pattern. The diffusing angles are specified as W x L.	
Angle Bending Diffuser	Angle Bending Diffusers both redirect and diffuse incident light, ideal for creating diffuse lighting in space-constrained environments.	