

**TECHSPEC® 50.8mm Dia., 3.18mm Thick, NIR I AR Coated Sapphire Window**



Stock **#39-261** 3-4 DAYS

- 1 + **€442,50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-24                      |
| €442,50                       |
| Qty 25+                       |
| €354,00                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Abbe Number (v<sub>d</sub>):**  
72.24

**Axis Orientation:**  
Random

**Bevel:**  
Protective as needed

|                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------|
| <b>Birefringence (<math>n_o</math>-<math>n_e</math>):</b><br>0.008 for Visible Light Orthogonal to Optical Axis |
| <b>Clear Aperture (%)</b> :<br>≥90                                                                              |
| <b>Clear Aperture CA (mm)</b> :<br>45.72                                                                        |
| <b>Diameter (mm)</b> :<br>50.80 ±0.05                                                                           |
| <b>Thickness (mm)</b> :<br>3.18 ±0.05                                                                           |
| <b>Coating</b> :<br>NIR I (600-1050nm)                                                                          |
| <b>Coating Specification</b> :<br>R <sub>avg</sub> ≤0.5% @ 600 - 1050nm                                         |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C)</b> :<br>8.8                                       |
| <b>Density (g/cm³)</b> :<br>3.97                                                                                |
| <b>Edges</b> :<br>Fine Ground                                                                                   |
| <b>Index of Refraction <math>n_d</math></b> :<br>1.77                                                           |
| <b>Knoop Hardness (kg/mm²)</b> :<br>1900                                                                        |
| <b>Parallelism (arcmin)</b> :<br>≤3.5                                                                           |
| <b>Poisson's Ratio</b> :<br>0.27                                                                                |
| <b>Substrate</b> :<br>Sapphire (Al <sub>2</sub> O <sub>3</sub> )                                                |
| <b>Surface Flatness (P-V)</b> :<br>2λ (typical)                                                                 |
| <b>Surface Quality</b> :<br>80-50                                                                               |
| <b>Type</b> :<br>Protective Window                                                                              |
| <b>Wavelength Range (nm)</b> :<br>600 - 1050                                                                    |
| <b>Young's Modulus (GPa)</b> :<br>435                                                                           |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |