

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 5.0mm Diameter X 10.0mm FL, 633nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock #88-998 3-4 DAYS

[Other Coating Options](#)

1

€53,50

ADD TO CART

Qty 1-9

€53,50

Qty 10+

€48,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
5.00 +0.0/-0.025

|                                                                                                   |
|---------------------------------------------------------------------------------------------------|
| <b>Effective Focal Length EFL (mm):</b><br>10.00 @ 587.6nm                                        |
| <b>Back Focal Length BFL (mm):</b><br>8.92                                                        |
| <b>Coating:</b><br>Laser V-Coat (633nm)                                                           |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 633nm                                  |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                               |
| <b>Surface Quality:</b><br>40-20                                                                  |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                             |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                       |
| <b>Focal Length Tolerance (%):</b><br>±1                                                          |
| <b>Centering (arcmin):</b><br><3                                                                  |
| <b>Center Thickness CT (mm):</b><br>1.64 ±0.05                                                    |
| <b>Edge Thickness ET (mm):</b><br>1.00                                                            |
| <b>Radius R<sub>1</sub> (mm):</b><br>5.17                                                         |
| <b>Clear Aperture CA (mm):</b><br>4.5                                                             |
| <b>f/#:</b><br>2.00                                                                               |
| <b>Numerical Aperture NA:</b><br>0.25                                                             |
| <b>Design Wavelength DWL (nm):</b><br>633                                                         |
| <b>Type:</b><br>Plano-Convex Lens                                                                 |
| <b>Bevel:</b><br>Protective bevel as needed                                                       |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm <sup>2</sup> @ 633nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |