

50mm FL Ultra High Resolution Fixed Focal Length Lenses



#68-684



Stock **#68-687** 2 In Stock

[Similar Products](#)

-

1

+

€1.505⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.505,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Series:

ltra High Resolution Fixed Focal Length Lenses

Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
77.00	Length (mm):
38.0	Maximum Diameter (mm):
38	Outer Diameter (mm):
170.00	Weight (g):
Optical Properties	
13.9	Field of View @ Min Working Distance (mm):
13.9mm - 7.3°	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
50.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/2.8 - f/16	Aperture (f/#):
<-0.02%	Maximum Distortion (%):
VS	Lens Wavelength Range:
Sensor	
2/3"	Maximum Sensor Format:
2.40	Pixel Size (µm):
Threading & Mounting	
M30.5 x 0.50	Filter Thread:
C-Mbunt	Mount:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

PRODUCT DETAILS

- 2/3", C-Mount Lens
- Up to 10 MegaPixels, 2.4µm Pixel Size Sensors
- Spectral Range of 400 - 1000nm
- 5mm to 50mm Focal Lengths

Ultra High Resolution Fixed Focal Length Lenses are designed to provide 10 MegaPixel resolution on axis. These lenses have a spectral range of 400 to 1000nm. Through the use of a floating focus and aspheric lens elements, these high-resolution lenses are able to maintain excellent performance from 100mm to infinity. Ultra High Resolution Fixed Focal Length Lenses feature locking focus, iris rings, and a front filter thread to allow the use of standard optical filters for increased versatility. The lenses are available in 7 focal length options and feature very low distortion.