

TECHSPEC® 515, 1030nm, 12.7mm Dia., Dual Band Low GDD Mirror



Stock #17-286 3-4 DAYS

⊖ 1 ⊕ **€159,00**

ADD TO CART

Qty 1-5
€159,00

Qty 6+
€141,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
45

Coating:
Ultrafast (500-540, 1000-1070nm)

Design Wavelength DWL (nm):
515, 1030

Diameter (mm):

12.70 +0/-0.1
Substrate: Fused Silica (Coming 7980)
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Mirror
Typical Applications: Beam transport of 1st and 2nd harmonic of Yb:doped lasers
Parallelism (arcmin): <3
Clear Aperture (%): >86
Back Surface: Commercial Polish
Coating Specification: R _s >99.9% @500-540nm R _p >99.8% @507-527nm R _s >99.9% @1000-1070nm R _p >99.8% @1005-1070nm
Wavelength Range (nm): 500 - 540, 1000 - 1070
Surface Flatness (P-V): <λ/8 @ 632.8nm over 9mm aperture
Coating Type: S1: Dielectric S2: Stress-compensating
GDD Specification: <35fs ² @ 500 - 540nm (s-pol) <50fs ² @ 510 - 525nm (p-pol) <20fs ² @ 1000 - 1070nm (s-pol) <40fs ² @ 1010 - 1055nm (p-pol)

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View