

# Coherent® StingRay™ Line Generator 1231494 | 520nm, 5mW, 45° Fan Angle

See More by [Coherent®](#)



Stock #86-852 1 In Stock

-

1

+

€1.155<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €1.155,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Product Downloads



## SPECIFICATIONS

General

|                                                                                                                                                                                                                                      |                                |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|
| Coherent®                                                                                                                                                                                                                            | Manufacturer:                  |
| Diode                                                                                                                                                                                                                                | Type of Laser:                 |
|                                                                                                                                                                                                                                      |                                |
| II                                                                                                                                                                                                                                   | Laser Class - CDRH:            |
| 1231494                                                                                                                                                                                                                              | Model Number:                  |
| Physical & Mechanical Properties                                                                                                                                                                                                     |                                |
| <10                                                                                                                                                                                                                                  | Pointing Stability (µrad/°C):  |
| 97.80                                                                                                                                                                                                                                | Length (mm):                   |
| Optical Properties                                                                                                                                                                                                                   |                                |
| TEM <sub>00</sub>                                                                                                                                                                                                                    | Spatial Mode:                  |
| 520.00                                                                                                                                                                                                                               | Wavelength (nm):               |
| <1.5                                                                                                                                                                                                                                 | Mode Quality, M <sup>2</sup> : |
| ±10                                                                                                                                                                                                                                  | Wavelength Tolerance (nm):     |
|                                                                                                                                                                                                                                      |                                |
| Green                                                                                                                                                                                                                                | Color:                         |
| 45.00                                                                                                                                                                                                                                | Fan Angle (°):                 |
| Electrical                                                                                                                                                                                                                           |                                |
| 5                                                                                                                                                                                                                                    | Output Power (mW):             |
| Max Analog: 500                                                                                                                                                                                                                      | Modulation Frequency (kHz):    |
| Hardware & Interface Connectivity                                                                                                                                                                                                    |                                |
| Power Supply:<br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#86-878</a><br>Europe: <a href="#">#86-878</a><br>Japan: <a href="#">#86-878</a><br>Korea: <a href="#">#86-878</a><br>China: <a href="#">#86-878</a> |                                |
| Electrical Leads/ Pin Connections:<br>Hirose HR-10P-12S                                                                                                                                                                              |                                |
| Free Space                                                                                                                                                                                                                           | Output Type:                   |
| 5 - 24 DC                                                                                                                                                                                                                            | Input Voltage (V):             |
| Environmental & Durability Factors                                                                                                                                                                                                   |                                |
| 10 to 40                                                                                                                                                                                                                             | Operating Temperature (°C):    |
| -20 to +60                                                                                                                                                                                                                           | Storage Temperature (°C):      |
| Regulatory Compliance                                                                                                                                                                                                                |                                |
| <a href="#">Compliant</a>                                                                                                                                                                                                            | RoHS 2015:                     |
| <a href="#">View</a>                                                                                                                                                                                                                 | Certificate of Conformance:    |

## PRODUCT DETAILS

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

**Note:** For CDRH certified systems (Class IIb), [#86-878](#) Laser Controller and additional external voltage source (0.5–5V) with BNC connector is required.

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we

provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---