

TECHSPEC[®] 50mm Diameter Protected Gold Coated, λ/10 Mirror



Stock **#64-033** 2 In Stock

-

1

+

€257^{,00}

ADD TO CART

Volume Pricing	
Qty 1-5	€257,00 each
Qty 6-25	€205,00 each
Qty 26-49	€192,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Flat Mirror

Type:

Physical & Mechanical Properties	
50.00 +0.00/-0.20	Diameter (mm):
Commercial Polish	Back Surface:
+0.0/-0.20	Dimensional Tolerance (mm):
Protective as needed	Bevel:
90	Clear Aperture (%):
Ground	Edges:
30	Parallelism (arcsec):
5.00 ±0.20	Thickness (mm):

Optical Properties	
λ/10	Surface Flatness (P-V):
Fused Silica (Corning 7980)	Substrate: □
20-10	Surface Quality:
R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm	Coating Specification:
Protected Gold (700-10000nm)	Coating:
Metal	Coating Type:
0.7 - 10	Wavelength Range (μm):
700 - 10000	Wavelength Range (nm):
0.8 J/cm² @ 1064nm, 10ns	Damage Threshold, Reference: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Precision Fused Silica Substrate
 - Variety of Sizes and Coating Options Available
 - Low Coefficient of Thermal Expansion
- TECHSPEC® λ/10 First Surface Mirrors are ideal for demanding beam steering and reflection applications in the visible and IR spectra. With a precision fused silica substrate, the mirrors feature a low coefficient of thermal expansion while being highly durable and resistant to abrasion. These precision mirrors are available in a variety of sizes and coating options, including enhanced aluminum, protected gold, and protected silver. These coatings allow for improved handling of the component, increased durability of the metal coating, and protection from oxidation with little impact to the performance on the metal coating. TECHSPEC® λ/10 First Surface Mirrors can be utilized in various optics and photonics applications, including biotech instruments such as DNA sequencers and polymerase chain reaction (PCR) testing platforms.
- Note:** Surface flatness is measured before coating.

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS

