


58 x 60mm Lenslet Array, 7 x 5.4mm Lenslets



Multi-Lens Arrays



Stock **#63-231** 20+ In Stock

-

1

+

€117⁴²

ADD TO CART

Volume Pricing	
Qty 1-10	€117,42 each
Qty 11-25	€91,67 each
Qty 26-49	€86,52 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Lens Array		Type:
Physical & Mechanical Properties		
58.0 x60.0		Dimensions (mm):
22.00 ±2%		Radius of Lenslet (mm):
3.00 ±0.2		Thickness (mm):
Optical Properties		
41.90		Effective Focal Length EFL (mm):
B270		Substrate: 
BBAR (400-700nm)		Coating:
400 - 700		Wavelength Range (nm):
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:

PRODUCT DETAILS

- Integrated, Monolithic Design
- Single Sided Arrays Create Even Illumination in Pairs
- Double Sided Arrays Ideal for Laser Top Hat Profile Generation

Multi-Lens Arrays are an all glass monolithic design which yields higher transmission, superior stability, and affordability when compared to cemented or plastic varieties. These lenses are available as single-sided or double-sided arrays to meet requirements for illumination, projection, and laser systems. The single-sided arrays are used to create square spot patterns or to create even illumination when used in pairs. Decreasing the spacing between the two lens arrays will increase the illuminated area while increasing the spacing will decrease the area. Double sided lens arrays are ideal for use with laser sources to create top hat output profiles, ensuring uniform illumination for machine vision and microscopy applications.

TECHNICAL INFORMATION

A	B	C	D	Stock No.
46.06mm	46.06mm	4mm	3mm	#63-230
58mm	60mm	7mm	5.4mm	#63-231
