

TECHSPEC[®] 5mm Aluminum & UV-VIS, High Tolerance Fused Silica Right Angle Prism



TECHSPEC High Tolerance UV Fused Silica Right Angle Prisms

Stock **#47-800** [CONTACT US](#)

-

1

+

€128⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€128,00 each
Qty 6-25	€102,00 each
Qty 26-49	€96,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Right Angle Prism

Physical & Mechanical Properties

Dimensional Tolerance (mm):
+0.0/-0.1

Bevel:

Protective as needed	
Length of Hypotenuse (mm):	
7.10	
Length of Legs (mm):	
5.00	
Optical Properties	
Angle Tolerance (arcsec):	
±40	
Coating:	
UV-VIS & Aluminized	
Substrate: ☐	
Fused Silica (Corning 7980)	
Surface Quality:	
20-10	
Pyramid Tolerance (arcmin):	
±1	
Image Orientation:	
Left-Handed	
Coating Specification:	
Legs: R _{abs} ≤1.0% @ 350 - 450nm, R _{avg} ≤1.5% @ 250 - 700nm	
Hypotenuse: R _{avg} >85% @ 400 - 700nm w/Black Overpaint	
Wavelength Range (nm):	
250 - 700	
Damage Threshold, By Design: ☐	
Hypotenuse: 0.3 J/cm2 @ 532 & 1064nm, 10ns	
Legs: 3 J/cm2 @ 355nm, 10ns; 5 J/cm2 @ 532nm, 10ns	
Power (fringes) @ 632.8nm:	
1.25	
Irregularity (fringes) @ 632.8nm:	
0.20	


Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 235:	
Compliant	

Product Details

- Ray Deviation of 90°
- Left Handed Image
- ±40 Arcseconds Angle Tolerance
- Additional [Right Angle Prism](#) Options Available

TECHSPEC® High Tolerance Fused Silica Right Angle Prisms, like most right angle prisms, are used to bend image paths or redirect light at 90°. This produces a left-handed image and depending on the orientation of the prism, the image may be inverted or reverted. Right angle prisms can also be used in combination for image/beam displacement. TECHSPEC® High Tolerance Fused Silica Right Angle Prisms feature low arcsecond angle tolerance and are made from precision UV fused silica for use in a variety of UV, Visible and NIR applications. The prisms are offered in leg lengths from 5 to 25mm.

Technical Information



UV FS Transmission Curve

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness

- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

;