

[See all 10 Products in Family](#)

## 50mW, 405nm Fiber-Coupled Laser Module



Stock #19-477 **5 In Stock**

- 1 + €870<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-9	€870,00 each
Qty 10+	€783,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads



### General

Type of Laser:  
Diode

Laser Class - CDRH:  
Class IIIb

### Physical & Mechanical Properties

Length of Fiber (m):

151.00 Length (mm):

## Optical Properties

Fiber-Coupled Spatial Mode:

405.00 ±5 Wavelength (nm):

Violet Color:

## Electrical

50 Output Power (mW):

## Hardware & Interface Connectivity

5.0 Operating Voltage (V):

Fiber-Coupled Output Type:

SMA Connector:

## Environmental & Durability Factors

+15 to +30 Operating Temperature (°C):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 233:

## Product Details

- 400µm Core Multimode Fiber with SMA Connector
- 50 and 100mW Output Power Options
- VIS and NIR Wavelengths Available
- [Free Space Alignment Lasers](#) Also Available

Fiber-Coupled Laser Modules feature an integrated 1m long, 400µm core fiber with an SMA905 connector. These cost-effective lasers provide up to 100mW of output power and have a long expected lifetime of 5000 hours. Fiber-Coupled Laser Modules are ideal for use in laser alignment, laser pointing, and laser measurement applications where a free-spaced laser diode module may be difficult to position. These lasers' compact size and easy operation make them well suited for integration into OEM systems.

**Note:** Power supply is sold separately.